

LANmark-OF Method B MPO-MPO Pre-Term LSZH APAC

- Factory terminated MTP-MTP fibre assembly
- Flexible fan-out for ease of installation in patch panel
- Small cable diameter reduces required data centre space
- Method B polarity Pre-Term
- Optimized for 40G/100G parallel transmission
- Fibre count: 12F, 24F, 48F, 96F
- Fibre type: OM3, OM4 and Singlemode (OS2 G.657.A1)

Pre-Term for data centres, buildings and campus based on Micro-Bundle Universal

The cable has a small diameter and bend radius to meet data centre requirements.

Fire performance

The cables have been tested for fire performance according to IEC 60332-3c. The cable meets LSZH requirements.

MPO-MPO Pre-Term characteristics

The Pre-Term has standard pinned (male) MPO connectors. This matches with the un-pinned (female) connectors in the female Plug&Play MPO-LC modules.

In order to reduce overlengths in data centers the Pre-Terms are custom made and available with 1m increments. The "xxx" in the N-number is the length in metre between the cable glands, i.e. the Pre-Term length between the back side of the patch panels.

The Pre-Terms are optimized for both pulling and laying in data centers. On both sides the MPO connectors are protected by a bubble foam. The maximum pulling force on the pulling eye is 450N. Pre-term are ordered with 2 options available: Pulling eye on one side or No pulling eye. A detachable pulling eye with corrugated tube can be ordered separately using PN N890.100HP.

The MPO Pre-Terms come with a PG-13 cable gland that fits into the LANmark-OF Plug&Play patch panel gland holders.

Optical Performance and Polarity

The insertion loss for a multimode the MPO connection has typical Low Loss performance of 0,2 dB and with a maximum



STANDARDS

ANSI/TIA-568-C.3
ISO/IEC 11801

of 0,35 dB insertion loss.

The insertion loss for a singlemode the MPO connection has typical performance of 0.5dB with a maximum of 0.75dB insertion loss.

The insertion loss of a MPO connection is measured according to standard IEC61300-3-45.

The minimum return loss for a multimode MPO connection is 20 dB and singlemode MPO connection is 45 dB, both measured according to IEC 61300-3-6.

The method B Pre-Term has a key up / key up design. This is in agreement with standard TIA-568.3-D-2016 method B.

LANmark-OF Method B MPO-MPO Pre-Term LSZH APAC

EIGENSCHAFTEN

Konstruktionsmerkmale

Fasertyp	OM3 50/125
Halogenfrei	Ja

Abmessungsmerkmale

Anzahl der optischen Fasern	48
Außendurchmesser, nom.	5.4 mm

Mechanische Eigenschaften

Mechanische Festigkeit gegen Schläge	10 impacts of 3 N.m
Querdruckwiderstand (IEC 794-1-E3)	100 N/cm
Maximale Zugspannung bei Installation	660 N

Übertragungseigenschaften

Insertion Loss, maximum, dB	0.35 dB
Rückflusdämpfung, max. dB	20 dB

Anwendungsmerkmale

Betriebstemperatur	-20...60 °C
flammwidrig	IEC 60332-3-24 (cat C)
Rauchdichte	IEC 61034
Minimaler Biegeradius bewegt	20 (xD)
Biegeradius min. nach Verlegung (xD)	10

Product list

Aginode ref.	Country ref.	Name	Fasertyp	Anzahl der optischen Fasern
☎ N145.BL48LAxxx-LA	-	LANmark-OF METHOD B MPO/M-MPO/M Pre-Term MM OM3 48c Low Loss LSZH xxxM Aqua Pulling Eye one side	OM3 50/125	48
☎ N145.BL24LAxxx-LA	-	LANmark-OF METHOD B MPO/M-MPO/M Pre-Term MM OM3 24c Low Loss LSZH xxxM Aqua Pulling Eye one side	OM3 50/125	24
☎ N145.BL12LAxxx-LA	-	LANmark-OF METHOD B MPO/M-MPO/M Pre-Term MM OM3 12c Low Loss LSZH xxxM Aqua Pulling Eye one side	OM3 50/125	12
☎ N147.BL96LAxxx-LA	-	LANmark-OF METHOD B MPO/M-MPO/M Pre-Term MM OM4 96c Low Loss LSZH xxxM Aqua Pulling Eye one side	OM4 50/125	96
☎ N147.BL48LAxxx-LA	-	LANmark-OF METHOD B MPO/M-MPO/M Pre-Term MM OM4 48c Low Loss LSZH xxxM Aqua Pulling Eye one side	OM4 50/125	48
☎ N147.BL24LAxxx-LA	-	LANmark-OF METHOD B MPO/M-MPO/M Pre-Term MM OM4 24c Low Loss LSZH xxxM Aqua Pulling Eye one side	OM4 50/125	24
☎ N147.BL12LAxxx-LA	-	LANmark-OF METHOD B MPO/M-MPO/M Pre-Term MM OM4 12c Low Loss LSZH xxxM Aqua Pulling Eye one side	OM4 50/125	12
☎ N144.BL96SAxxx-LY	-	LANmark-OF METHOD B MPO/M-MPO/M Pre-Term SM OS2 G.657.A1 96c LSZH xxxM Yellow Pulling Eye one side	SM (G657.A1)	96
☎ N144.BL48SAxxx-LY	-	LANmark-OF METHOD B MPO/M-MPO/M Pre-Term SM OS2 G.657.A1 48c LSZH xxxM Yellow Pulling Eye one side	SM (G657.A1)	48
☎ N144.BL24SAxxx-LY	-	LANmark-OF METHOD B MPO/M-MPO/M Pre-Term SM OS2 G.657.A1 24c LSZH xxxM Yellow Pulling Eye one side	SM (G657.A1)	24
☎ N144.BL12SAxxx-LY	-	LANmark-OF METHOD B MPO/M-MPO/M Pre-Term SM OS2 G.657.A1 12c LSZH xxxM Yellow Pulling Eye one side	SM (G657.A1)	12

☎ = Make to order, 🏠 = In Stock

All drawings, designs, specifications, plans and particulars of weights, size and dimensions contained in the technical or commercial documentation of Aginode is indicative only and shall not be binding on Aginode or be treated as constituting a representation on the part of Aginode.