

LANmark-OF Method C MPO-MPO Pre-Term LSZH APAC

- Factory terminated MTP-MTP fibre assembly
- Flexible fan-out for ease of installation in patch panel
- Small cable diameter reduces required data centre space
- Method C polarity Pre-Term
- Only one type of patch cords and one type of cassettes required for duplex transmission
- Fibre count: 12F, 24F, 48F, 96F
- Fibre type: OM3, OM4 and Singlemode (OS2 G.657.A1)

Pre-Term for data centres, buildings and campus based on Micro-Bundle Universal

The cable has a small diameter and bend radius to meet data centre requirements.

Fire performance

The cables have been tested for fire performance according to IEC 60332-3c. The cable meets LSZH requirements.

MPO-MPO Pre-Term characteristics

The Pre-Term has standard pinned (male) MPO connectors. This matches with the un-pinned (female) connectors in the female Plug&Play MPO-LC modules.

In order to reduce overlengths in data centers the Pre-Terms are custom made and available with 1m increments. The "xxx" in the N-number is the length in metre between the cable glands, i.e. the Pre-Term length between the back side of the patch panels.

The Pre-Terms are optimized for both pulling and laying in data centers. On both sides the MPO connectors are protected by a bubble foam. The maximum pulling force on the pulling eye is 450N. Pre-term are ordered with 2 options available: Pulling eye on one side or No pulling eye. A detachable pulling eye with corrugated tube can be ordered separately using PN N890.100HP.

The MPO Pre-Terms come with a PG-13 cable gland that fits into the LANmark-OF Plug&Play patch panel gland holders.

Optical Performance and Polarity

The insertion loss for a multimode the MPO connection has typical Low Loss performance of 0,2 dB and with a maximum



STANDARDS

ISO/IEC 11801

ANSI/TIA-568.3-D

of 0,35 dB insertion loss.

The insertion loss for a singlemode the MPO connection has typical performance of 0.5dB with a maximum of 0.75dB insertion loss.

The insertion loss of a MPO connection is measured according to standard IEC61300-3-45.

The minimum return loss for a multimode MPO connection is 20 dB and singlemode MPO connection is 45 dB, both measured according to IEC 61300-3-6.

The method B Pre-Term has a pairflip key up / key down design. This is in agreement with standard TIA-568.3-D-2016 method C.

LANmark-OF Method C MPO-MPO Pre-Term LSZH APAC

CARACTÉRISTIQUES

Caractéristiques de construction

Type de fibres optiques	SM (G657.A1)
Sans halogène	Oui

Caractéristiques dimensionnelles

Nombre de fibres optiques	24
Diamètre externe nominal (mm)	5.4 mm

Caractéristiques mécaniques

Résistance mécanique aux chocs	10 impacts of 3 N.m
Résistance à l'écrasement (IEC 794-1-E3)	100 N/cm
Tension maximale à l'installation	660 N

Caractéristiques de transmission

Insertion Loss, maximum, dB	0.75 dB
Return Loss, Minimum, dB	20 dB

Caractéristiques d'utilisation

Température ambiante d'utilisation, plage	-20...60 °C
Non propageur de l'incendie	IEC 60332-3-24 (cat C)
Densité de fumée dégagée	IEC 61034
Rayon de courbure minimum en utilisation dynamique	20 (xD)
Minimum bending radius, static (XD)	10

Product list

Aginode ref.	Country ref.	Name	Type de fibres optiques	Nombre de fibres optiques
☎ N144.CL24SAxxx-LY	-	LANmark-OF METHOD C MPO/M-MPO/M Pre-Term SM OS2 G.657.A1 24c LSZH xxxM Yellow Pulling Eye one side	SM (G657.A1)	24
☎ N144.CL12SAxxx-LY	-	LANmark-OF METHOD C MPO/M-MPO/M Pre-Term SM OS2 G.657.A1 12c LSZH xxxM Yellow Pulling Eye one side	SM (G657.A1)	12
☎ N145.CL48LAxxx-LA	-	LANmark-OF METHOD C MPO/M-MPO/M Pre-Term MM OM3 48c Low Loss LSZH xxxM Aqua Pulling Eye one side	OM3 50/125	48
☎ N145.CL24LAxxx-LA	-	LANmark-OF METHOD C MPO/M-MPO/M Pre-Term MM OM3 24c Low Loss LSZH xxxM Aqua Pulling Eye one side	OM3 50/125	24
☎ N145.CL12LAxxx-LA	-	LANmark-OF METHOD C MPO/M-MPO/M Pre-Term MM OM3 12c Low Loss LSZH xxxM Aqua Pulling Eye one side	OM3 50/125	12
☎ N147.CL96LAxxx-LV	-	LANmark-OF METHOD C MPO/M-MPO/M Pre-Term MM OM4 96c Low Loss LSZH xxxM Aqua Pulling Eye one side	OM4 50/125	96
☎ N147.CL48LAxxx-LV	-	LANmark-OF METHOD C MPO/M-MPO/M Pre-Term MM OM4 48c Low Loss LSZH xxxM Aqua Pulling Eye one side	OM4 50/125	48
☎ N147.CL24LAxxx-LV	-	LANmark-OF METHOD C MPO/M-MPO/M Pre-Term MM OM4 24c Low Loss LSZH xxxM Aqua Pulling Eye one side	OM4 50/125	24
☎ N147.CL12LAxxx-LV	-	LANmark-OF METHOD C MPO/M-MPO/M Pre-Term MM OM4 12c Low Loss LSZH xxxM Violet Pulling Eye one side	OM4 50/125	12
☎ N144.CL96SAxxx-LY	-	LANmark-OF METHOD C MPO/M-MPO/M Pre-Term SM OS2 G.657.A1 96c LSZH xxxM Yellow Pulling Eye one side	SM (G657.A1)	96
☎ N144.CL48SAxxx-LY	-	LANmark-OF METHOD C MPO/M-MPO/M Pre-Term SM OS2 G.657.A1 48c LSZH xxxM Yellow Pulling Eye one side	SM (G657.A1)	48
☎ N145.CL96LAxxx-LA	-	LANmark-OF METHOD C MPO/M-MPO/M Pre-Term MM OM3 96c Low Loss LSZH xxxM Aqua Pulling Eye one side	OM3 50/125	96

☎ = Make to order, 🏠 = In Stock

All drawings, designs, specifications, plans and particulars of weights, size and dimensions contained in the technical or commercial documentation of Aginode is indicative only and shall not be binding on Aginode or be treated as constituting a representation on the part of Aginode.