

LANmark-OF ENSPACE Method B MTP-MTP Pre-Term LSZH APAC

LANMARK-OF ENSPACE METHOD B MTP/M-MTP/M PRE-TERM MM 24C LOW LOSS LSZH XXXM OM3 AQUA

Aginode Ref: N145.B24MMExxxA

- Factory terminated MTP-MTP fibre assembly
- Flexible fan-out for ease of installation in patch panel
- Small cable diameter reduces required data centre space
- Method B polarity Pre-Term
- Optimized for 40G/100G parallel transmission
- Fibre count: 24F
- Fibre type: Multimode OM3

Pre-Term for data centres, buildings and campus based on Micro-Bundle Universal

The cable has a small diameter and bend radius to meet data centre requirements.

Fire performance

The cables have been tested for fire performance according to IEC 60332-3c. The cable meets LSZH requirements.

MTP*-MTP Pre-Term characteristics

The MTP-MTP Pre-Term has standard pinned (male) connectors. This matches with the un-pinned (female) connectors in the ENSPACE modules and the female Plug&Play modules.

In order to reduce overlengths in data centers the Pre-Terms are custom made and available with 1m increments. The "xxx" in the N-number is the length in metre between the cable glands, i.e. the Pre-Term length between the back side of the patch panels.

The Pre-Terms are optimized for both pulling and laying in data centers. On both sides the MTP connectors are protected by a bubble foam. The maximum pulling force on the pulling eye is 450N. The detachable pulling eye with corrugated tube can be ordered using PN N890.100HP.

The MTP-MTP Pre-Terms come with a PG-13 cable gland that fits into the LANmark-OF ENSPACE and Plug&Play patch panel slots.



STANDARDS

ANSI/TIA-568-C.3
ISO/IEC 11801

All drawings, designs, specifications, plans and particulars of weights, size and dimensions contained in the technical or commercial documentation of Aginode is indicative only and shall not be binding on Aginode or be treated as constituting a representation on the part of Aginode.

Optical Performance and Polarity

The insertion loss for a multimode the MTP-MTP* connection has Low Loss performance: typical insertion loss is 0,15 dB with a maximum of 0,35 dB insertion loss. Ultra Low loss is also available with typical insertion loss 0.125dB with a maximum of 0.25dB insertion loss.

The insertion loss for a singlemode the MTP-MTP* connection has Low Loss performance: typical insertion loss 0.3dB with a maximum of 0.35dB insertion loss.

The insertion loss of a MTP-MTP* connection is measured according to standard IEC61300-3-45.

The minimum return loss for a multimode MTP connection is 20 dB measured according to IEC 61300-3-6. The minimum return loss for a singlemode MTP connection is 45 dB measured according to IEC 61300-3-6.

The method B Pre-Term has a key up / key up design. This is in agreement with standard TIA-568.3-D-2016 method B.

LANmark-OF ENSPACE METHOD B MTP/M-MTP/M Pre-Term MM 24c Low Loss LSZH xxxM OM3 Aqua

Caractéristiques

Caractéristiques de construction

Type de fibres optiques	OM3 50/125
Sans halogène	Oui

Caractéristiques dimensionnelles

Nombre de fibres optiques	24
Diamètre externe nominal (mm)	5.4 mm

Caractéristiques mécaniques

Résistance mécanique aux chocs	10 impacts of 3 N.m
Résistance à l'écrasement (IEC 794-1-E3)	100 N/cm
Tension maximale à l'installation	660 N

Caractéristiques de transmission

Insertion Loss, maximum, dB	0.35 dB
Return Loss, Minimum, dB	20 dB

Caractéristiques d'utilisation

Température ambiante d'utilisation, plage	-20...60 °C
Non propageur de l'incendie	IEC 60332-3-24 (cat C)
Densité de fumée dégagée	IEC 61034
Rayon de courbure minimum en utilisation dynamique	20 (xD)
Minimum bending radius, static (XD)	10