

LANmark-OF MPO-MPO Pre-Term OFNP Method B APAC

- Factory terminated MPO-MPO fibre assembly
- Flexible fan-out for ease of installation in patch panel
- Small cable diameter reduces required data centre space
- Method B polarity Pre-Term
- Optimized for 40G/100G parallel transmission applications
- Fibre count: 12F, 24F, 48F, 96F
- Fibre type: OM3, OM4 and singlemode (OS2 G.657.A1)

Pre-Term for data centres, buildings and campus based on Micro-Bundle.

The cable has a small diameter and bend radius to meet data centre requirements.

Fire performance

The cables have been tested for fire performance according to Plenum rated, providing a very high fire performance with minimal fire load and can be used in air flow space.

MPO-MPO Pre-Term characteristics

The MPO-MPO Pre-Term has standard pinned (male) connectors. This matches with the un-pinned (female) connectors in the female Plug&Play modules.

In order to reduce overlengths in data centers the Pre-Terms are custom made and available with 1m increments. The "xxx" in the N-number is the length in metre between the cable glands, i.e. the Pre-Term length between the back side of the patch panels.

After the cable gland the Pre-Term has a fan-out. The fan-out splits the cable into tubes. The tubes are reinforced with aramid yarns. At the end of each tube a MPO-connectors is mounted. The jacket of the tube is the same colour as the cable jacket. Close to the MPO-connector a label is installed to identify the number of the leg.

Pre-terminated MPO fibre cable can be ordered separately with a removable pulling eye for fast deployment onsite. The pulling eye provides minimum 450N installation tension. High crush resistant pulling eye is also available with a high strength protection tube. The removable pulling eye can be quickly detached after installation and can be reinstalled, reducing construction waste and making it more suitable for sustainable



STANDARDS

ISO/IEC 11801

ANSI/TIA-568.3-D

All drawings, designs, specifications, plans and particulars of weights, size and dimensions contained in the technical or commercial documentation of Aginode is indicative only and shall not be binding on Aginode or be treated as constituting a representation on the part of Aginode.

environmental protection. Prefabricated pulling eye is also available with the MPO pre-term. The detachable pulling eye with corrugated tube can be ordered using PN N890.100HP.

The MPO-MPO Pre-Terms come with a PG-13 cable gland that fits into the LANmark-OF ENSPACE and Plug&Play patch panel slots.

Optical Performance and Polarity

The insertion loss for a multimode the MPO-MPO connection has Ultra Low Loss performance: typical insertion loss is 0,2 dB with a maximum of 0,35 dB insertion loss.

The typical insertion loss for a singlemode the MPO-MPO connection is 0,5 dB with a maximum of 0,75 dB insertion loss.

The insertion loss of a MPO-MPO connection is measured according to standard IEC61300-3-45.

The minimum return loss for a multimode MPO connection is 20 dB . The minimum return loss for a singlemode MPO connection is 45 dB. The measurement is according to IEC 61300-3-6.

MPO cable standard is METHOD B. Other common standards recognized by ISO/IEC 11801 and TIA 568 standards are available, such as METHOD A, METHOD B, METHOD C, etc.

LANmark-OF MPO-MPO Pre-Term OFNP Method B APAC

CHARACTERISTICS

구조적 특성

Fiber optic type OM4 50/125

치수

Number of optical fibres 24

기계적 특성

Mechanical resistance to impacts 10 impacts of 3 N.m

Crush resistance (IEC 60794-1-E3) 100 N/cm

Maximum installation tension 660 N

Transmission characteristics

Insertion Loss, maximum, dB 0.25 dB

Return Loss, Minimum, dB 27 dB

사용 특성

操作温度范围 -20...60 °C

Minimum dynamic operating bending radius 20 (xD)

Minimum bending radius, static (XD) 10

Product list

Aginode ref.	Country ref.	이름	Fiber optic type	Number of optical fibres
☎ N147.BU24UPxxx-PA	-	LANmark-OF METHOD B MPO/M-MPO/M Pre-Term MM OM4 24c Ultra low loss OFNP xxxM Aqua	OM4 50/125	24
☎ N144.BU24UPxxx-PY	-	LANmark-OF METHOD B MPO/M-MPO/M Pre-Term SM OS2 G.657.A1 24c Ultra Low loss OFNP xxxM Yellow	SM (G657.A1)	24
☎ N147.BU12UAxxx-PA	-	LANmark-OF METHOD B MPO/M-MPO/M Pre-Term MM OM4 12c Ultra low loss OFNP xxxM Aqua	OM4 50/125	12
☎ N144.BU12LAxxx-PY	-	LANmark-OF METHOD B MPO/M-MPO/M Pre-Term SM OS2 G.657.A1 12c Ultra Low loss OFNP xxxM Yellow	SM (G657.A1)	12
☎ N144.BU48SPxxx-PY	-	LANmark-OF METHOD B MPO/M-MPO/M Pre-Term SM OS2 G.657.A1 48c OFNP xxxM Yellow	SM (G657.A1)	48
☎ N144.BU96SAxxx-PY	-	LANmark-OF METHOD B MPO/M-MPO/M Pre-Term SM OS2 G.657.A1 96c OFNP xxxM Yellow pulling eye one side	SM (G657.A1)	96
☎ N145.BU12LPxxx-PA	-	LANmark-OF METHOD B MPO/M-MPO/M Pre-Term MM OM3 12c OFNP xxxM Aqua	OM3 50/125	12
☎ N145.BU24LPxxx-PA	-	LANmark-OF METHOD B MPO/M-MPO/M Pre-Term MM OM3 24c OFNP xxxM Aqua	OM3 50/125	24
☎ N145.BU48LPxxx-PA	-	LANmark-OF METHOD B MPO/M-MPO/M Pre-Term MM OM3 48c OFNP xxxM Aqua	OM3 50/125	48
☎ N145.BU96LAxxx-PA	-	LANmark-OF METHOD B MPO/M-MPO/M Pre-Term MM OM3 96c OFNP xxxM Aqua Pulling eye one side	OM3 50/125	96
☎ N147.BU12LPxxx-PA	-	LANmark-OF METHOD B MPO/M-MPO/M Pre-Term MM OM4 12c OFNP xxxM Aqua	OM4 50/125	12
☎ N147.BU24LPxxx-PA	-	LANmark-OF METHOD B MPO/M-MPO/M Pre-Term MM OM4 24c OFNP xxxM Aqua	OM4 50/125	24
☎ N147.BU48LPxxx-PA	-	LANmark-OF METHOD B MPO/M-MPO/M Pre-Term MM OM4 48c OFNP xxxM Aqua	OM4 50/125	48
☎ N147.BU96LAxxx-PA	-	LANmark-OF METHOD B MPO/M-MPO/M Pre-Term MM OM4 96c OFNP xxxM Aqua pulling eye one side	OM4 50/125	96
☎ N144.BU12SPxxx-PY	-	LANmark-OF METHOD B MPO/M-MPO/M Pre-Term SM OS2 G.657.A1 12c OFNP xxxM Yellow	SM (G657.A1)	12
☎ N144.BU24SPxxx-PY	-	LANmark-OF METHOD B MPO/M-MPO/M Pre-Term SM OS2 G.657.A1 24c OFNP xxxM Yellow	SM (G657.A1)	24

☎ = Make to order, 📦 = In Stock

All drawings, designs, specifications, plans and particulars of weights, size and dimensions contained in the technical or commercial documentation of Aginode is indicative only and shall not be binding on Aginode or be treated as constituting a representation on the part of Aginode.